LEXPLAST TROWEL

Rubberized Flashing Cement

DESCRIPTION & USE

LEXPLAST TROWEL is a chemically modified roof flashing cement reinforced with select polymers.

- Used to stop leaks on metal or asphalt surfaces, to repair and stick modified bitumen SBS membranes
- Repairs cracks in the flashing and helps prevent leaks around the eaves
- Can be used as shingle tab cement

FEATURES & BENEFITS

- Strong 100% adhesion to wet surfaces when tested in accordance with ASTM D3409
- Flexible Exceptionally high percentage of elongation and retraction

LIMITATIONS

- Do not use on coal tar EPDM membranes or other shingle roofs.
- Cover vent ducts before application and during the drying period.
- Do not dilute.
- FLAMMABLE! Keep away from heat and open flame.
- Avoid all contact with skin and avoid breathing in the fumes or spray.
- Do not use indoors.

INSTALLATION

- 1. After removing all dust, grease or oil, apply even coats (1/8" to 1/4" thick) on dry surfaces with a trowel.
- 2. Apply 1/4" thick coats or more on wet surfaces to stop the leak.
- 3. Press down to ensure strong adhesion.
- 4. Cover all vent ducts before applying the product and until the mastic has dried completely.
- 5. Consult the material safety data sheet before using.
- 6. Wear safety equipment during application.



TECHNICAL DATA

Format	3 gal (11,36 L)
Approximate weight	28 lbs
Non-volatile solid substance per weight	75.0%
Volatile solvent per weight	25.0%
Mineral filler and/or other stabilizers per weight	20%
Moisture content per volume	0.05%
Net weight	8.5 lbs/gal
Layer thickness without absortion, on a 50 ft. per gallon application ratio	77 mils
Drying time	2 days Ouside shell
Application temperature	-34°C to 65°C (-30°F to +150°F
Performance at 60°C (140°F), ASTM D 4586	No sagging, No blistering
Performance at 0°C (32°F), ASTM D 4586	No cracking No separation
Flash point, ASTM D93	40°C min. (104°F min.)
Condition in the pail	Homogenous
Elongation @ 22°C (73°F)	270% min.
Coverage for 1/8" thickness	13 ft sq.

Visit our video channels: https://vimeo.com/channels/lexcoren

